

GRC58, Mechanical Ground Rod Clamp, Cable to Rod

By Burndy
Catalog # [GRC58](#)

Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 10 AWG (Sol)- 1 AWG (Str), 5/8" Drive Rod, 3/8" Stud



Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets

Application

For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	RUS
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	Yes
Certification - UL Listed Direct Burial	Yes

Conductor

Conductor - Rod Size	5/8 in
Conductor - Copper Solid Size Range	10 AWG
Conductor Size	#10 AWG Sol - #1 AWG Str
Conductor - Copper Str Size Range	12 AWG-1 AWG

Conductor Type

- Rod-Size
- CU C Solid-Size

Dimensions

Package Length	7.100 in
Package Width	6.500 in
Package Weight	12.630 lb.
Dimension - Height inch	2.18 in
Package Height	4.750 in
Dimension - Height mm	55.6 mm
Dimension - Width inch	0.95 in
Dimension - Width mm	24 mm
Dimension - B Length inch	0.57 in
Dimension - Length Side B inch	0.63 in

General

Material - Hardware	Silicon Bronze
Sub Brand	MECHANICAL CONNECTOR
Plated	N
Type	GRC, High Strength
UPC 12 Digit	781810230961
UPC 14 Digit GTIN	00781810230961
Hardware Type	Silicon Bronze
Material	Copper Alloy
Plating Type	Unplated
UPC	781810230961

Logistics

Minimum Pack Quantity	1
Carton Quantity	100
Pallet Quantity	10000

Product Assets

[Catalog \[English\]](#)