



GRC58916CF, Mechanical Ground Rod Clamp, Cable to Rod

By Burndy
Catalog # [GRC58916CF](#)

Cu Grounding Rod Connector, Suitable for Direct Burial, 9/16 IN Stud, Cu Cable to Rod, 5/8 IN Rod (Run), 10 AWG Sol - 1 AWG Str. (Tap), Hex Head Bolts Available.



General

Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	781810662090
UPC 12 Digit	7818106620900

Dimensions

Bolt Size	9/16 in
Dimension - B Length inch	0.57 in
Dimension - Height inch	2.18 in
Dimension - Width inch	0.92 in
Dimension - Width mm	23 mm

Conductor Related

Conductor - Rod Size	5/8 in
Conductor Size	#10 AWG Sol - #1 AWG Str
Conductor Type	<ul style="list-style-type: none">Rod-SizeCU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50034869](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GRC58916CF-SPEC-EN | REV 5/2024