

GRF4C3, Universal Grounding Clamp, 1 or 2 Conductors to Round or Square Pedestal

By Burndy
Catalog # GRF4C3



Universal Grounding Clamp, 1 or 2 Nos of Conductors, 8 AWG-2 AWG, Pedestal Type : 1" (Round), Upto 7/8" (Square), 3/8" Stud.

Features

- One connector fits all applications
- Ease of specification and installation
- Single bolt design with no need to disassemble
- Single wrench installation
- Accepts 1 or 2 ground conductors
- Requires less connectors to install signal reference grid
- Tin plated cast bronze construction
- Resists corrosion and provides extended life ground connection
- Grounds all pedestals (round or square)
- Will accept up to 7/8" Square and up to 1" Round
- Serves 3 needs: Signal Reference Grid, Static Ground, Fault Current Ground
- UNIGROUND™ connector will solve all ground problems found in computer applications today
- UL467 Listed for the US and Canadian Markets

Application

For Raised Floor Systems

General

Catalog Number	GRF4C3
EU RoHS Indicator	Yes
Installation Torque	100 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round;Square
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	UNIGROUND
Trade Name	UNIGROUND™
Type	GRF
UPC	781810828021
UPC 12 Digit	781810828021

Dimensions

Dimension - B Length inch	1.96 in
Dimension - Height inch	3.14 in
Dimension - Width inch	1.76 in
Dimension - Width mm	45 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor - Pipe or Round Tube Size	3/8 ;1/2 ;3/4 ;1
Conductor - Pipe or Round Tube Size Range	3/8 in -1 in
Conductor - Pipe or Square Tube Size	1/2 ;5/8 ;3/4 ;7/8
Conductor - Pipe or Square Tube Size Range	1/2 in -7/8 in
Number of Conductors	1;2

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - GRF4C3_MODEL-IGES](#)

[3D Models - GRF4C3_MODEL-PDF](#)

[3D Models - GRF4C3_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_grfla](#)

[Sales Drawings - sd201716-01](#)

[Specifications - GRF4C3](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-GRF4C3-SPEC-EN | REV 8/2024