



GRL4, Ground Rod Clamp, Light Duty, Cable to Rod

By Burndy
Catalog # [GRL4](#)



Copper Alloy Light Duty Economical Ground Rod Clamp, 2-10 AWG, 1/2-Rod Size.

Features

- UL467 Listed
- Acceptable for Direct Burial in earth or concrete

Application

For Direct Burial

General

Catalog Number	GRL4
EU RoHS Indicator	Yes
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRL, Light Duty
UPC	781810051818
UPC 14 Digit GTIN	00781810051818

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Conductor Related

Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Rod Size	1/2 in
Conductor Size	#2 AWG - #10 AWG

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_GRL_Lineart](#)
[Sales Drawings - SC209790-01](#)
[Specifications - GRL4](#)



A Hubbell brand