



GRL5, Ground Rod Clamp, Light Duty, Cable to Rod

By Burndy
Catalog # [GRL5](#)

Mechanical Grounding Connector, 10 AWG - 2 AWG, 5/8" Ground Rod.



Features

- UL467 Listed
- Acceptable for Direct Burial in earth or concrete

Application

For Direct Burial

General

Catalog Number	GRL5
EU RoHS Indicator	Yes
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRL, Light Duty
UPC	781810051825
UPC 12 Digit	7818100518255

Conductor Related

Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Rod Size	5/8 in
Conductor Size	#2 AWG - #10 AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Minimum Pack Quantity	1

Product Assets

- [3D Models - GRL5_MODEL-IGES](#)
- [3D Models - GRL5_MODEL-PDF](#)
- [3D Models - GRL5_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GRL_Lineart](#)
- [Sales Drawings - SC209790-01](#)
- [Specifications - GRL5](#)