



GRL6, Ground Rod Clamp, Light Dute, Cable to Rod

By Burndy
Catalog # [GRL6](#)



Light Duty Economical Ground Rod Clamp,CU, 2-10 AWG, 3/4" Rod Size.

Application

For Direct Burial

General

EU RoHS Indicator	Yes
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRL, Light Duty
UPC	781810051832
UPC 12 Digit	7818100518322

Conductor Related

Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Rod Size	3/4 in
Conductor Size	#2 AWG - #10 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - GRL6_MODEL-IGES](#)
- [3D Models - GRL6_MODEL-PDF](#)
- [3D Models - GRL6_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_GRL_Lineart](#)
- [Sales Drawings - SC209790-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GRL6-SPEC-EN | REV 5/2024