



GSTUD12HY Structural Steel Ground Stud

By Burndy
Catalog # [GSTUD12HY](#)

Structural Steel Grounding Connector; Accommodates: 1/0 AWG; 1/2" Rod; Copper Coated; Nickel Plated.



Features

- May be welded to steel surfaces quickly and easily
- No disk grinding needed
- Knurled surface for better gripping
- Copper plated
- May be installed during adverse weather conditions

General

Material	Steel
Plated	Y
Plating Type	Nickel
Trade Name	VERSITAIL™
UPC	781810274187
UPC 12 Digit	7818102741877

Dimensions

Dimension - B Length fraction	25/49 in
Dimension - B Length inch	0.51 in
Dimension - D inch	1.25 in
Dimension - Ground Rod Size	1/2 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.80 in
Physical Attribute - Tongue Angle	45 Degree

Conductor Related

Conductor - Copper Str Size Range	1/0 AWG
Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in
Conductor Type	<ul style="list-style-type: none">• Rod-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	3920

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd..086414-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GSTUD12HY-SPEC-EN | REV 5/2024