

GZ4C38, Mechanical Grounding Connector, Copper Cable to Bar

By Burndy
Catalog # [GZ4C38](#)



Mechanical Grounding Connector, For Copper Cable to Bar, 8 AWG (Str) - 4 (Str), 3/8" Stud.

Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets

Application

For Joining A Wide Range Of Copper Cable To Bar, Direct Burial In Concrete Or Ground

General

Catalog Number	GZ4C38
EU RoHS Indicator	Yes
Installation Torque	240 in-lb
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GZ
UPC	781810260753
UPC 14 Digit GTIN	00781810260753

Dimensions

Bolt Size	3/8 in
Dimension - Bar Thickness inch	0.25 in
Dimension - Bar Thickness mm	6 mm
Dimension - Height fraction	1-1/2
Dimension - Height inch	1.50 in
Dimension - Height mm	38.1 mm
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - Width fraction	1-1/8 in

Dimension - Width inch	1.06 in
Dimension - Width mm	27 mm

Conductor Related

Conductor - Copper Str Size	8;7;6;5;4
Conductor - Copper Str Size Range	8 AWG - 4 AWG
Conductor Range	#8 AWG (Str) to #4 AWG (Str)

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	40
-----------------------	----

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_gzla](#)
[Sales Drawings - SD208785-01](#)
[Specifications - GZ4C38](#)