



HSB100FR, Heat Shrink Tubing, 1" ID Min.(Exp.), 0.5" ID Max.(Rec.), 1/0-4/0 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V.



By Burndy
Catalog # [HSB100FR](#)

Heat Shrink Tubing, 1" ID Min.(Exp.), 0.5" ID Max.(Rec.), 1/0-4/0 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V.

Application

For Terminations And Splices

General

Connector Type	THIN WALL TUBES/REELS
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	HEAT SHRINK
Type	HS-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810265741

Conductor Related

Conductor Range	#1/0 AWG to #4/0 AWG
Conductor Size	4/0AWG - 300kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSB100FR-SPEC-EN | REV 5/2024