



HSB110H48PF5, Cross-Linked Polyolefin Heat Shrinkable Heavy Wall Tube, 1 - 3/0 AWG, 1000 V, Shrink Ratio: 3 : 1.

By Burndy
Catalog # HSB110H48PF5

Cross-Linked Polyolefin Heat Shrinkable Heavy Wall Tube, 1 - 3/0 AWG, 600 V, Shrink Ratio: 3 : 1.

Application

For Direct Burial

General

Catalog Number	HSB110H48PF5
Connector Type	HEAVY WALL TUBES
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-H-PF, Heavy Wall, Flame Retardant
UPC	781810214909

Conductor Related

Conductor Range	#1 AWG to #3/0 AWG
Conductor Size	1AWG - 3/0AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Number of Pieces in Package	5

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB35H6PF25_LineArt](#)
- [Sales Drawings - SD211942-01](#)
- [Specifications - HSB110H48PF5](#)
- [Video - Heat Shrink Product Overview & Installation](#)