



HSB112FR100, Heat Shrink Tubing, 1.50" ID Min.(Exp.), 0.75" ID Max. (Rec.), 250-500 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V. 100 Ft Reel.



By Burndy
Catalog # [HSB112FR100](#)

Heat Shrink Tubing, 1.50" ID Min.(Exp.), 0.75" ID Max.(Rec.), 250-500 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V. 100 Ft Reel.

General

Catalog Number	HSB112FR100
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810265772

Conductor Related

Conductor Range	250-500 Kcmil
Conductor Size	350kcmil - 750kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSB112FR100](#)



A Hubbell brand