

## HSB12FR, PVC Thin Wall Black Heat Shrink Tubing, #1-#4 Code, #4-#6 Flex, 600 V, Fire Retardant.

By Burndy  
Catalog # [HSB12FR](#)



PVC Thin Wall Black Heat Shrink Tubing, #1-#4 Code, #4-#6 Flex, 600 V, Fire Retardant.

### Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

### Application

For Terminations And Splices

### General

Catalog Number	HSB12FR
Connector Type	THIN WALL TUBES/REELS
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	HEAT SHRINK
Type	HS-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810265789

### Dimensions

Thickness	0.03
-----------	------

### Conductor Related

Conductor Range	#6 AWG to #4 AWG
Conductor Size	4AWG - 1AWG

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)  
[Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)  
[Sales Drawings - 50015598](#)  
[Specifications - HSB12FR](#)