



HSB12T1200PF, Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max. (Rec.), Polyolefin, Thin Wall, Black, Shrink ratio-2:1, 600V, 100 Ft Reel.



By Burndy
Catalog # [HSB12T1200PF](#)

Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max.(Rec.),
Polyolefin, Thin Wall, Black, Shrink ratio-2:1, 600V, 100 Ft Reel.

General

Catalog Number	HSB12T1200PF
Material	POLYOLEFIN
UPC	781810242421

Conductor Related

Conductor Range	#6 AWG to #2 AWG
-----------------	------------------

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
[Sales Drawings - SD211941](#)
[Specifications - HSB12T1200PF](#)