



# HSB12T300PF, Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.12" ID Max. (Rec.), 6-2 AWG, Cross Linked Polyolefin, Thin Wall, Flame Retardant, Black, 600V.



By Burndy  
Catalog # [HSB12T300PF](#)

Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.12" ID Max.(Rec.), 6-2 AWG, Cross Linked Polyolefin, Thin Wall, Flame Retardant, Black, 600V.

## Application

For Terminations And Splices

## General

Catalog Number	HSB12T300PF
Connector Type	THIN WALL REEL
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810213735

## Conductor Related

Conductor Range	#6 AWG to #2 AWG
Conductor Size	6AWG - 2AWG

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB38T300PF\\_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSB12T300PF](#)



A Hubbell brand