



HSB14FR250, Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.13" ID Max. (Rec.), #12 - #10, PVC, Fire retardant, Thin Wall, Black, 250 Ft Reel.



By Burndy
Catalog # [HSB14FR250](#)

Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.13" ID Max.(Rec.), #12 - #10, PVC, Fire retardant, Thin Wall, Black, 250 Ft Reel.

General

Catalog Number	HSB14FR250
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810265826

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12AWG -8AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSB14FR250](#)
- [Video - Heat Shrink Product Overview & Installation](#)



A Hubbell brand