



HSB18FR250, Heat Shrink Tubing, 0.13" ID Min.(Exp.), 0.06" ID Max. (Rec.), #16 - #14, PVC, Fire retardant, Thin Wall, Black, 250 Ft Reel.



By Burndy
Catalog # [HSB18FR250](#)

Heat Shrink Tubing, 0.13" ID Min.(Exp.), 0.06" ID Max.(Rec.), #16 - #14, PVC, Fire retardant, Thin Wall, Black, 250 Ft Reel.

General

Catalog Number	HSB18FR250
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810265888

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16AWG - 14AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM

UL Listed No

Logistics

Minimum Pack Quantity 16

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSB18FR250](#)
- [Video - Heat Shrink Product Overview & Installation](#)