



HSB316T300PF, Heat Shrink Tubing, 0.19" ID Min.(Exp.), 0.09" ID Max. (Rec.), 18-12 AWG, Thin Wall, Black

By Burndy

Catalog # [HSB316T300PF](#)



Heat Shrink Tubing, 0.19" ID Min.(Exp.), 0.09" ID Max.(Rec.), 18-12 AWG, Cross Linked Polyolefin, Thin Wall, Flame Retardant, Black, 600V.

Application

For Terminations And Splices

General

Catalog Number	HSB316T300PF
Connector Type	THIN WALL REEL
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810213520

Conductor Related

Conductor Size	18AWG - 12AWG
----------------	---------------

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSB316T300PF](#)



A Hubbell brand