



HSB316T6PF18, Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing, #12-18 AWG, 600 V, 6.00" L, Flame Retardant, All Black.

By Burndy
Catalog # [HSB316T6PF18](#)



Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing, #12-18 AWG, 600 V, 6.00" L, Flame Retardant, All Black.

Application

For Terminations And Splices

General

EU RoHS Indicator	Yes
Material	POLYOLEFIN
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810214527

Conductor Related

Conductor Range	#18 AWG to #12 AWG
-----------------	--------------------

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	180
Minimum Pack Quantity	1
Number of Pieces in Package	18

Product Assets

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Product Cross Section Image\(s\) - BUR_HSB38T30OPF_LineArt](#)
[Sales Drawings - SD211941](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSB316T6PF18-SPEC-EN | REV 5/2024