



HSB332T6PF24, Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing, #16-18 AWG, 600 V, 6.00" L, Flame Retardant, All Black.



By Burndy
Catalog # [HSB332T6PF24](#)

Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing, #16-18 AWG, 600 V, 6.00" L, Flame Retardant, All Black.

Application

For Terminations And Splices

General

Catalog Number	HSB332T6PF24
EU RoHS Indicator	Yes
Material	POLYOLEFIN
Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810214411

Conductor Related

Conductor Range	#18 AWG to #16 AWG
-----------------	--------------------

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	240
Minimum Pack Quantity	1
Number of Pieces in Package	24

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSB332T6PF24](#)
- [Video - Heat Shrink Product Overview & Installation](#)