



HSB34FR250, Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.375" ID Max. (Rec.), #2 - 1/0, PVC, Fire retardant, Thin Wall, Black, 250 Ft Reel.



By Burndy
Catalog # [HSB34FR250](#)

Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.375" ID Max.(Rec.), #2
- 1/0, PVC, Fire retardant, Thin Wall, Black, 250 Ft Reel.

General

Catalog Number	HSB34FR250
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810265949

Conductor Related

Conductor Range	#2 AWG to # 1/0 AWG
Conductor Size	1/0AWG - 3/0AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSB34FR250](#)



A Hubbell brand