



HSB34H48PF5, Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max.(Rec.), 6-2 AWG, Heavy Wall, Black, 4" Length

By Burndy
Catalog # [HSB34H48PF5](#)



Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max.(Rec.), 6-2 AWG, Cross Linked Polyolefin, Heavy Wall, Flame Retardant, Black, 1000V,4" Length.

Application

For Direct Burial

General

| | |
|-------------------|--------------------------------------|
| Connector Type | HEAVY WALL TUBES |
| EU RoHS Indicator | Yes |
| Material | Cross-linked Polyolefin |
| Sub Brand | HEAT SHRINK |
| Type | HS-H-PF, Heavy Wall, Flame Retardant |
| UPC | 781810214893 |

Conductor Related

| | |
|-----------------|------------------|
| Conductor Range | #6 AWG to #2 AWG |
| Conductor Size | 6AWG - 2AWG |

Certifications And Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------------|---|
| Carton Quantity | 5 |
| Minimum Pack Quantity | 1 |
| Number of Pieces in Package | 5 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB35H6PF25_LineArt](#)
- [Sales Drawings - SD211942-01](#)
- [Video - Heat Shrink Product Overview & Installation](#)



A proud member of the Hubbell Family.