



**HSB34H6PF10, Heat Shrink Tubing,  
0.75" ID Min.(Exp.), 0.22" ID Max.  
(Rec.), #6 - 2, Polyolefin, Thick  
Wall, Black, Shrink ratio-3:1, 600V.**



By Burndy  
Catalog # [HSB34H6PF10](#)

Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max.(Rec.), #6 - 2, Polyolefin, Thick Wall, Black, Shrink ratio-3:1, 600V.

**General**

|                |                         |
|----------------|-------------------------|
| Catalog Number | HSB34H6PF10             |
| Connector Type | HEAVY WALL TUBES        |
| Material       | Cross-linked Polyolefin |
| UPC            | 781810214800            |

**Conductor Related**

|                 |                  |
|-----------------|------------------|
| Conductor Range | #6 AWG to #2 AWG |
| Conductor Size  | 6AWG - 2AWG      |

**Certifications And Compliance**

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |

UL Listed Yes

**Logistics**

|                       |     |
|-----------------------|-----|
| Carton Quantity       | 250 |
| Minimum Pack Quantity | 1   |

**Product Assets**

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB35H6PF25\\_LineArt](#)
- [Sales Drawings - SD211942-01](#)
- [Specifications - HSB34H6PF10](#)
- [Video - Heat Shrink Product Overview & Installation](#)