



# HSB34H9PF10, Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max. (Rec.), #6 - 2, Polyolefin, Thick Wall, Black, Shrink ratio-3:1, 600V.



By Burndy  
Catalog # HSB34H9PF10

Heat Shrink Tubing, 0.75" ID Min.(Exp.), 0.22" ID Max.(Rec.), #6 - 2, Polyolefin, Thick Wall, Black, Shrink ratio-3:1, 600V.

## Application

Direct burial applications

## General

Catalog Number	HSB34H9PF10
Connector Type	HEAVY WALL TUBES
Construction Material - Main	Polyolefin
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Temperature Rating	-55° C to 135° C
Type	HS-H-PF
UPC	781810214817

## Dimensions

Length 9 in

## Electrical Ratings

Voltage Rating 600 V

## Conductor Related

Conductor Range #6 AWG to #2 AWG  
Conductor Size 6AWG - 2AWG

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	250
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB35H6PF25\\_LineArt](#)
- [Sales Drawings - SD211942-01](#)
- [Specifications - HSB34H9PF10](#)
- [Video - Heat Shrink Product Overview & Installation](#)