



HSB35H3PF25, Heat Shrink Tubing, 0.35" ID Min.(Exp.), 0.12" ID Max. (Rec.), 14-10 AWG, Heavy Wall, Black

By Burndy
Catalog # HSB35H3PF25

Heat Shrink Tubing, 0.35" ID Min.(Exp.), 0.12" ID Max.(Rec.), 14-10 AWG, Cross Linked Polyolefin, Heavy Wall, Flame Retardant, Black, 1000V.

Application

For Direct Burial

General

Catalog Number	HSB35H3PF25
Connector Type	HEAVY WALL TUBES
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	HEAT SHRINK
Type	HS-H-PF, Heavy Wall, Flame Retardant
UPC	781810214763

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Conductor Size	14AWG - 10AWG

Certifications And Compliance

Buy American Compliant	No
------------------------	----

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	625
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB35H6PF25_LineArt](#)
- [Sales Drawings - SD211942-01](#)
- [Specifications - HSB35H3PF25](#)
- [Video - Heat Shrink Product Overview & Installation](#)