



HSB38T300PF, Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max. (Rec.), #8 - #6, Polyolefin, Thin Wall, Black, 25 Ft Reel.

By Burndy
Catalog # [HSB38T300PF](#)



Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8
- #6, Polyolefin, Thin Wall, Black, 25 Ft Reel.

General

Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213667

Conductor Related

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Customer Notices - Prop 65 Notice](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Sales Drawings - SD211941](#)



A proud member of the Hubbell Family.