



HSB38T6PF12, Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max. (Rec.), #8 - #6, Polyolefin, Thin Wall, Black, Shrink ratio-2:1.

By Burndy
Catalog # [HSB38T6PF12](#)



Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8
- #6, Polyolefin, Thin Wall, Black, Shrink ratio-2:1.

General

Material POLYOLEFIN
UPC 781810214541

Conductor Related

Conductor Range #8 AWG to #6 AWG

Certifications And Compliance

Certification - CSA Approved Yes
Certification - ETL No
Standards - RoHS Compliance CM
Status
UL Listed No

Logistics

Carton Quantity 120
Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
[Sales Drawings - SD211941](#)
[Video - Heat Shrink Product Overview & Installation](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSB38T6PF12-SPEC-EN | REV 5/2024