



# HSBL100T300PF, Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max.(Rec.), 2/0 - 300, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.



By Burndy  
Catalog # [HSBL100T300PF](#)

Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max.(Rec.), 2/0 - 300, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

## General

Catalog Number	HSBL100T300PF
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810214022

## Conductor Related

Conductor Range	#2/0 AWG - 300 Kcmil
Conductor Size	2/0AWG - 300kcmil

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)  
[Product Cross Section Image\(s\) - BUR\\_HSB38T300PF\\_LineArt](#)  
[Sales Drawings - SD211941](#)  
[Specifications - HSBL100T300PF](#)