



**HSBL100T48PF, Heat Shrink Tubing,
1.00" ID Min.(Exp.), 0.50" ID Max.
(Rec.), 2/0 - 300, Polyolefin, Thin
Wall, Blue, Shrink ratio-2:1, 4 Ft
Reel.**



By Burndy
Catalog # [HSBL100T48PF](#)

Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max.(Rec.), 2/0
- 300, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 4 Ft Reel.

General

Catalog Number	HSBL100T48PF
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810212905

Conductor Related

Conductor Range	#2/0 AWG - 300 Kcmil
Conductor Size	2/0AWG - 300kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSBL100T48PF](#)