



HSBL116T300PF, Heat Shrink Tubing, 0.06" ID Min.(Exp.), 0.03" ID Max.(Rec.), #18, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

By Burndy
Catalog # [HSBL116T300PF](#)



Heat Shrink Tubing, 0.06" ID Min.(Exp.), 0.03" ID Max.(Rec.), #18, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

General

Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213186

Conductor Related

Conductor Range	#18 AWG
Conductor Size	18AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Sales Drawings - SD211939-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSBL116T300PF-SPEC-EN | REV 6/2024