



HSBL14T300PF, Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.125" ID Max. (Rec.), #14 - 10, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.



By Burndy
Catalog # [HSBL14T300PF](#)

Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.125" ID Max.(Rec.), #14 - 10, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

General

Catalog Number HSBL14T300PF
Connector Type THIN WALL REEL
Material Cross-linked Polyolefin
UPC 781810213643

Conductor Related

Conductor Range #14 AWG to #10 AWG
Conductor Size 14AWG - 10AWG

Certifications And Compliance

Certification - CSA Approved Yes
Certification - ETL No
Standards - RoHS Compliance CM
Status
UL Listed No

Logistics

Minimum Pack Quantity 10

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
[Sales Drawings - SD211941](#)
[Specifications - HSBL14T300PF](#)