



HSBL150T48PF, Heat Shrink Tubing, 1.50" ID Min.(Exp.), 0.75" ID Max.(Rec.), 2/0 - 350, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 4 Ft Reel.



By Burndy
Catalog # [HSBL150T48PF](#)

Heat Shrink Tubing, 1.50" ID Min.(Exp.), 0.75" ID Max.(Rec.), 2/0 - 350, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 4 Ft Reel.

General

Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213001

Conductor Related

Conductor Range	#2/0 AWG - 350 Kcmil
Conductor Size	250kcmil - 500kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Product Cross Section Image\(s\) - BUR_HSB38T30OPF_LineArt](#)
[Sales Drawings - SD211941](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-HSBL150T48PF-SPEC-EN | REV 5/2024