



HSBL18T300PF, Heat Shrink Tubing, 0.125" ID Min.(Exp.), 0.62" ID Max. (Rec.), #18 - 14, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.



By Burndy
Catalog # [HSBL18T300PF](#)

Heat Shrink Tubing, 0.125" ID Min.(Exp.), 0.62" ID Max.(Rec.), #18 - 14, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

General

Catalog Number	HSBL18T300PF
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213506

Conductor Related

Conductor Range	#18 AWG to #14 AWG
Conductor Size	18AWG - 14AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
[Sales Drawings - SD211941](#)
[Specifications - HSBL18T300PF](#)