



# HSBL316T300PF, Heat Shrink Tubing, 0.187" ID Min.(Exp.), 0.093" ID Max.(Rec.), #18 - 12, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.



By Burndy  
Catalog # [HSBL316T300PF](#)

Heat Shrink Tubing, 0.187" ID Min.(Exp.), 0.093" ID Max.(Rec.), #18 - 12, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

## General

Catalog Number	HSBL316T300PF
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213575

## Conductor Related

Conductor Range	#18 AWG to #12 AWG
Conductor Size	18AWG - 12AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB38T300PF\\_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSBL316T300PF](#)