



# HSBL332T300PF, Heat Shrink Tubing, 0.094" ID Min.(Exp.), 0.046" ID Max.(Rec.), #18 - 16, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

By Burndy  
Catalog # [HSBL332T300PF](#)



Heat Shrink Tubing, 0.094" ID Min.(Exp.), 0.046" ID Max.(Rec.), #18 - 16, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

## General

Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213407

## Conductor Related

Conductor Range	#18 AWG to #16 AWG
Conductor Size	18AWG - 16AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)  
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)  
[Sales Drawings - SD211939-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-HSBL332T300PF-SPEC-EN | REV 5/2024