



HSBL34T300PF, Heat Shrink Tubing, 0.750" ID Min.(Exp.), 0.375" ID Max.(Rec.), #1 - 3/0, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.



By Burndy
Catalog # [HSBL34T300PF](#)

Heat Shrink Tubing, 0.750" ID Min.(Exp.), 0.375" ID Max.(Rec.), #1 - 3/0, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

General

Catalog Number HSBL34T300PF
Connector Type THIN WALL REEL
Material Cross-linked Polyolefin
UPC 781810213957

Conductor Related

Conductor Range #1 AWG to #3/0 AWG
Conductor Size 1AWG - 3/0AWG

Certifications And Compliance

Certification - CSA Approved Yes
Certification - ETL No
Standards - RoHS Compliance CM
Status

UL Listed No

Logistics

Minimum Pack Quantity 10

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSBL34T300PF](#)
- [Video - Heat Shrink Product Overview & Installation](#)