



**HSBL38T300PF, Heat Shrink  
Tubing, 0.375" ID Min.(Exp.), 0.187"  
ID Max.(Rec.), #8 - 6, Polyolefin,  
Thin Wall, Blue, Shrink ratio-2:1, 25  
Ft Reel.**



By Burndy  
Catalog # [HSBL38T300PF](#)

Heat Shrink Tubing, 0.375" ID Min.(Exp.), 0.187" ID Max.(Rec.), #8 - 6, Polyolefin, Thin Wall, Blue, Shrink ratio-2:1, 25 Ft Reel.

**General**

Catalog Number	HSBL38T300PF
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213711

**Conductor Related**

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

**Certifications And Compliance**

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance Status	CM
UL Listed	No

**Logistics**

Minimum Pack Quantity	10
-----------------------	----

**Product Assets**

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB38T300PF\\_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSBL38T300PF](#)