



## HSBLU12FR250, Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max. (Rec.), #6 - #4, Thin Wall, Blue, 250 Ft Reel

By Burndy  
Catalog # [HSBLU12FR250](#)

Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max.(Rec.), #6 - #4, PVC, Fire retardant, Thin Wall, Blue, Shrink ratio-2:1, 250 Ft Reel.

### General

Catalog Number	HSBLU12FR250
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266021

### Conductor Related

Conductor Range	#6 AWG to #4 AWG
Conductor Size	4AWG - 1AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No



### Logistics

Minimum Pack Quantity	2
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSBLU12FR250](#)



A Hubbell brand