

# HSC112FR, Heat Shrink Tubing, 1.5" ID Min.(Exp.), 0.75" ID Max.(Rec.), 250-500 Flex, PVC, Flame Retardant, Clear, 600V.



By Burndy  
Catalog # [HSC112FR](#)

Heat Shrink Tubing, 1.5" ID Min.(Exp.), 0.75" ID Max.(Rec.), 250-500 Flex, PVC, Flame Retardant, Clear, 600V.

## Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

## Application

Used on UL Recognized TO 600V

## General

Catalog Number	HSC112FR
Color	Clear
Connector Type	CLEAR TUBES
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Fire Retardant
UPC	781810266151

## Conductor Related

Conductor Range	250-500 Kcmil
Conductor Size	350kcmil - 750kcmil

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certified Listed	TAA Compliant (All status valid till December 2024)
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSC112FR](#)