

HSC112FR, Heat Shrink Tubing, 1.5" ID Min.(Exp.), 0.75" ID Max.(Rec.), 250-500 Flex, PVC, Flame Retardant, Clear, 600V.



By Burndy
Catalog # [HSC112FR](#)

Heat Shrink Tubing, 1.5" ID Min.(Exp.), 0.75" ID Max.(Rec.), 250-500 Flex, PVC, Flame Retardant, Clear, 600V.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

Used on UL Recognized TO 600V

General

Catalog Number	HSC112FR
Color	Clear
Connector Type	CLEAR TUBES
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Fire Retardant
UPC	781810266151

Conductor Related

Conductor Range	250-500 Kcmil
-----------------	---------------

Conductor Size	350kcmil - 750kcmil
----------------	---------------------

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSC112FR](#)