



HSC12T300PF, Heat Shrinkable Cross-Linked Thin Polyolefin Tube, 6 - 2 AWG, 600 V, Shrink Ratio: 2 : 1, Standard reel size: 25 ft.



By Burndy
Catalog # HSC12T300PF

Heat Shrinkable Cross-Linked Thin Polyolefin Tube, 6 - 2 AWG, 600 V, Shrink Ratio: 2 : 1, Standard reel size: 25 ft.

Application

For Terminations And Splices

General

Catalog Number	HSC12T300PF
Color	Clear
Connector Type	THIN WALL REEL
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	VISISHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810213803

Conductor Related

Conductor Range	#6 AWG to #2 AWG
Conductor Size	6AWG - 2AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSC12T300PF](#)