



## HSC14T300PF, Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.12" ID Max. (Rec.), 14-10 AWG, Thin Wall, Clear

By Burndy  
Catalog # [HSC14T300PF](#)



Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.12" ID Max.(Rec.), 14-10 AWG, Cross Linked Polyolefin, Thin Wall, Flame Retardant, Clear, 600V.

### Application

For Terminations And Splices

### General

Catalog Number	HSC14T300PF
Color	Clear
Connector Type	THIN WALL REEL
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	VISISHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810213605

### Conductor Related

Conductor Range	#14 AWG to #10 AWG
Conductor Size	14AWG - 10AWG

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB38T300PF\\_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSC14T300PF](#)