



HSC332T300PF, Thin Wall Cross-Linked Clear Polyolefin Heat Shrink Tubing, #16-18 AWG, 600 V, Flame Retardant.



By Burndy
Catalog # [HSC332T300PF](#)

Thin Wall Cross-Linked Clear Polyolefin Heat Shrink Tubing, #16-18 AWG, 600 V, Flame Retardant.

Application

For Terminations And Splices

General

Catalog Number	HSC332T300PF
Color	Clear
Connector Type	THIN WALL REEL
EU RoHS Indicator	Yes
Material	Cross-linked Polyolefin
Sub Brand	VISISHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
UPC	781810213360

Conductor Related

Conductor Range	#18 AWG to #16 AWG
Conductor Size	18AWG - 16AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSC332T300PF](#)