

HSC38FR, Vinyl Fire Retardant Clear Heat Shrink Tubing, #6-#4(Code) #8-#6(Flex), 600V.



By Burndy
Catalog # [HSC38FR](#)

Vinyl Fire Retardant Clear Heat Shrink Tubing, #6-#4(Code) #8-#6(Flex), 600V.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

General

Catalog Number	HSC38FR
Color	Clear
Connector Type	CLEAR TUBES
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810266304

Conductor Related

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG - 4AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - HSC38FR_MODEL-STEP](#)
- [3D Models - HSC38FR_MODEL-PDF](#)
- [3D Models - HSC38FR_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSC38FR](#)