



HSC38FR250, Clear heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - #6, PVC, Fire retardant, Thin Wall, Shrink ratio-2:1, 50 Ft Reel.



By Burndy
Catalog # [HSC38FR250](#)

Clear heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - #6, PVC, Fire retardant, Thin Wall, Shrink ratio-2:1, 50 Ft Reel.

Application

Excellent flame retardant properties and a 2:1 shrink ratio. Tubing enables inspectors to read die index embossments on installed connectors easily

General

Catalog Number	HSC38FR250
Color	Clear
Connector Type	CLEAR TUBES
Construction Material - Main	Polyvinyl Chloride
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	VISI-SHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR
UPC	781810266311

Conductor Related

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG - 4AWG

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSC38FR250](#)