



# HSC38T300PF, Clear Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - 6, Polyolefin, Thin Wall, Shrink ratio-2:1, 25 Ft Reel.



By Burndy  
Catalog # [HSC38T300PF](#)

Clear Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - 6, Polyolefin, Thin Wall, Shrink ratio-2:1, 25 Ft Reel.

## General

Catalog Number	HSC38T300PF
Color	Clear
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213674

## Conductor Related

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB38T300PF\\_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSC38T300PF](#)