



HSG100FR, Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max. (Rec.), 1/0 - 4/0, Thin Wall, Green, 25 Ft Reel



By Burndy
Catalog # [HSG100FR](#)

Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max.(Rec.), 1/0 - 4/0, PVC, Fire retardant, Thin Wall, Green, Shrink ratio-2:1, 25 Ft Reel.

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

General

Catalog Number	HSG100FR
Color	Green
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266328

Conductor Related

Conductor Range	#1/0 AWG to #4/0 AWG
Conductor Size	4/0AWG - 300kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	400
-----------------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSG100FR](#)