



# HSG100FR100, Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max. (Rec.), 1/0 - 4/0, Thin Wall, Green, 100 Ft Reel

By Burndy  
Catalog # [HSG100FR100](#)



Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max.(Rec.),  
1/0 - 4/0, PVC, Fire retardant, Thin Wall, Green, Shrink ratio-2:1,  
100 Ft Reel.

## General

Color	Green
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266335

## Conductor Related

Conductor Range	#1/0 AWG to #4/0 AWG
Conductor Size	4/0AWG - 300kcmil

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	70
-----------------------	----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)



A proud member of the Hubbell Family.