



## HSG112FR, Heat Shrink Tubing, 1.50" ID Min.(Exp.), 0.75" ID Max.(Rec.), 250 - 500, Thin Wall, Green, 25 Ft Reel

By Burndy  
Catalog # [HSG112FR](#)



Heat Shrink Tubing, 1.50" ID Min.(Exp.), 0.75" ID Max.(Rec.), 250 - 500, PVC, Fire retardant, Thin Wall, Green, Shrink ratio-2:1, 25 Ft Reel.

### Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

### General

Catalog Number	HSG112FR
Color	Green
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266342

### Conductor Related

Conductor Range	250-500 Kcmil
Conductor Size	350kcmil - 750kcmil

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	20
-----------------------	----

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSG112FR](#)