



# HSG12T48PF, Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max. (Rec.), #6 - 2, Polyolefin, Thin Wall, Green, Shrink ratio-2:1, 4 Ft Reel.



By Burndy  
Catalog # [HSG12T48PF](#)

Heat Shrink Tubing, 0.50" ID Min.(Exp.), 0.25" ID Max.(Rec.), #6 - 2, Polyolefin, Thin Wall, Green, Shrink ratio-2:1, 4 Ft Reel.

## General

|                |                         |
|----------------|-------------------------|
| Catalog Number | HSG12T48PF              |
| Color          | Green                   |
| Connector Type | THIN WALL REEL          |
| Material       | Cross-linked Polyolefin |
| UPC            | 781810212752            |

## Conductor Related

|                 |                  |
|-----------------|------------------|
| Conductor Range | #6 AWG to #2 AWG |
| Conductor Size  | 6AWG - 2AWG      |

## Certifications And Compliance

|                              |     |
|------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL          | No  |

|                             |    |
|-----------------------------|----|
| Standards - RoHS Compliance | CM |
| Status                      |    |
| UL Listed                   | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB38T300PF\\_LineArt](#)
- [Sales Drawings - SD211941](#)
- [Specifications - HSG12T48PF](#)