



# HSG14FR250, Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.13" ID Max. (Rec.), #12 - #10, PVC, Fire retardant, Thin Wall, Green, 250 Ft Reel.



By Burndy  
Catalog # [HSG14FR250](#)

Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.13" ID Max.(Rec.), #12 - #10, PVC, Fire retardant, Thin Wall, Green, 250 Ft Reel.

## General

Catalog Number	HSG14FR250
Color	Green
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810266397

## Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12AWG -8AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	40
-----------------------	----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSG14FR250](#)
- [Video - Heat Shrink Product Overview & Installation](#)